


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/19/13	D.GRIFFIN




CAPTIVE PLASTIC LID SCREWS(4X)

RIGHT SIDE VIEW

SECTION A-A




FRONT VIEW



THRU HOLES FOR MOUNTING ENCLOSURE USING #6 SCREWS (4X)

TOP VIEW LID REMOVED



INTERNAL BOSES FOR MOUNTING COMPONENTS OR DIN RAILS

- NOTE:
- 1- ENCLOSURE MATERIAL-GRAY (RAL7035) VALOX® 357U THERMOPLASTIC POLYESTER
 - 2- NEMA RATED TYPE 3, 3R, 3S, 4, 4X, 12 AND 13 PRIOR TO MODIFICATIONS.
 - 3- IEC 529 RATED IP 66 PRIOR TO MODIFICATION.
 - 4- HEAT DEFLECTION TEMPERATURE UP TO 138 DEG C.
 - 6- ENCLOSURES ARE MAINTENANCE FREE AND CORROSION RESISTANT.
 - 7- SHALL BE PACKAGED AS PER L-COM SPEC PKG-00095
 - 8- ALL DIMENSIONS FOR REFERENCE ONLY

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005 ANGULAR TOLERANCES: ALL = ± 1° PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY B.PUCHASKI	2/13/13		
	CHECKED BY P.PESA	2/13/13	CATEGORY ENCLOSURE	
	APPROVED BY P.PESA	2/13/13	PRODUCT DESCRIPTION PBT NEMA ENCLOSURE - 5 X 3 X 3 SCREW COVER	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. NBV533
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: NBV533.SLDDRW	REV. A
		SHEET 1 OF 1		