

## REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A1	UPDATED PER ECO-14720	07/09/2025	HBAKKE	GUTTADAURO

F

F

E

E

D

D

C


C

B


B

A


A



RJ11 JACK  
(6P4C)  
"J1"



HIGH-IMPACT ABS PLASTIC HOUSING, IVORY



RJ11 JACK  
(6P4C)  
"J2"

WIRE MAP	
"J1"	"J2"
2	5
3	4
4	3
5	2

## NOTES:

1. CROSS WIRED.
2. UL94V-0 FLAMMABILITY RATING.
3. JACK PIN PLATING: 15 MICROINCHES GOLD OVER NICKEL.
4. COMPONENT SHALL BE TESTED FOR CONTINUITY.
5. COMPONENT SHALL BE INDIVIDUALLY PACKAGED.

## REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:  
 $X = \pm .2$  [5]      FRACTIONS  
 $XX = \pm .02$  [0.5]       $\pm 1/32$   
 $XXX = \pm .005$  [0.13]      ANGLES  $\pm 1^\circ$

CABLE LENGTH TOLERANCES:  
 $\le 12$  [305] =  $\pm 1$  [25] / -0  
 $> 12$  [305]  $\le 60$  [1524] =  $\pm 2$  [51] / -0  
 $> 60$  [1524]  $\le 120$  [3048] =  $\pm 4$  [102] / -0  
 $> 120$  [3048]  $\le 300$  [7620] =  $\pm 6$  [152] / -0  
 $> 300$  [7620] =  $\pm 5\%$  / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**  
an INFINITE<sup>®</sup> brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5  
SCALE      SHEET  
NONE      1 OF 1

DESCRIPTION  
MODULAR COUPLER, RJ11 (6x4), CROSS WIRED

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	TJC	TDG1026-4R	A1