


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	REV A DRAWING RELEASED	09/28/2018	DFRISIELLO
B	ECN 9957: REVISED JACKET MARKING	07/08/2019	DFRISIELLO

TFPC6A-GRN

TFPC6A-GRN CONSISTS OF 1000 FEET OF CONTINUOUS LENGTH BULK CABLE



CROSS-SECTIONAL VIEW



COLOR CODE

- 1) BLUE x WHITE/BLUE
- 2) ORANGE x WHITE/ORANGE
- 3) GREEN x WHITE/GREEN
- 4) BROWN x WHITE/BROWN

NOTES:

1.CONSTRUCTION:

CONDUCTOR: 23 AWG SOLID BARE COPPER

PAIRS: COLOR CODED SINGLES TWISTED INTO PAIRS

CABLE: (4) TWISTED PAIRS TWISTED TOGETHER TO FORM A CABLE CORE WITH A SPLINE DIVIDER

SHIELD: AN ALUMINUM POLYESTER FOIL SHIELD (100% COVERAGE) OVER PE TAPE WRAP.

A SOLID TINNED COPPER DRAIN WIRE IN CONTACT WITH THE OUTER SURFACE.

JACKET: PLENUM, PVC, COLOR, GREEN, WITH RIP CORD

OVERALL CABLE DIAMETER:

0.268±0.012 [6.8 ±0.3mm]

2.PHYSICAL PROPERTIES:

TEMPERATURE RATING, MAX.

80°C

TEMPERATURE RATING, MIN.

-20°C

3.AGENCY APPROVALS:

NEC ARTICLE 800, UL 444 TYPE CMP RATING FT6, ETL VERIFIED TO ANSI-TIA 568.2 CATEGORY 6, C(ETL)US RoHS COMPLIANT

4. JACKET PRINT:

VERTICAL CABLE E191267 (UL) c(UL) CMP FT 75C 23AWG 4PR CAT6A F/UTP ANSI/TIA 568C.2 RoHS COMPLIANT XXXXFT

5. ELECTRICAL CHARACTERISTICS: (FOR 100m OF CABLE)

VOLTAGE RATING 30V

CAPACITANCE 5.6nF/100m NOMINAL

VELOCITY OF PROPAGATION 65%

MAX CONDUCTOR D.C. RESISTANCE 9.38 Ω/100m NOMINAL

MAX D.C. RESISTANCE, UNBALANCE 5%

6. CHARACTERISTIC IMPEDANCE

1 MHz - 100 MHz 100 ± 15%

101 MHz - 250 MHz 100 ± 22%

251 MHz - 550 MHz 100 ± 25%


7.PACKAGING:

CABLE SHIPPED ON A SPOOL

REGULATORY COMPLIANCE:

CE2011/65/EU(RoHS DIRECTIVE)

UL LISTED

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120 [3048] - 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 [5.08] .XX = .02 [51] .XXX = .005 [13]	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845	
	DRAWN BY DFRISIELLO	09/28/2018		
	CHECKED BY MPATEL	09/28/2018		
	APPROVED BY DGUTTADAUR	09/28/2018		
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY TELECOM/MODULAR	
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION Cat6a F/UTP 23SLD CMP GRN	
SIZE A	FSCM NO. 43321	DWG. NO. TFPC6A-GRN	REV. B	
SCALE: 1:4		CAD FILE: TFPC6A-GRN.SLDDRW		SHEET 1 OF 1