


REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	D	ECO-15404	01/16/2026	HBAKKE	DGUST



PART NUMBER	LENGTH	
	FEET	METERS
TRG608-T6T-05M	1.64	0.5
TRG608-T6T-1M	3.28	1.0
TRG608-T6T-2M	6.56	2.0
TRG608-T6T-3M	9.84	3.0
TRG608-T6T-5M	16.41	5.0
TRG608-T6T-10M	32.82	10.0
TRG608-T6T-15M	49.22	15.0

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
 $X = \pm .2$ [5]
 $XX = \pm .02$ [0.5]
 $XXX = \pm .005$ [0.13]

FRACTIONS
 $\pm 1/32$
 $\pm 1/64$

ANGLES $\pm 1^\circ$

CABLE LENGTH TOLERANCES:
 ≤ 12 [305] $\leq +1$ [25] / -0
 > 12 [305] ≤ 60 [1524] $\leq +2$ [51] / -0
 > 60 [1524] ≤ 120 [3048] $\leq +4$ [102] / -0
 > 120 [3048] ≤ 300 [7620] $\leq +6$ [152] / -0
 > 300 [7620] $\leq +5\%$ / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-COM
an INFINITE® brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE
NONE

1 OF 1

DESCRIPTION
CATEGORY 6A M12 8 POSITION X CODE SF/UTP INDUSTRIAL
CABLE, M12 M / M12 F

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DCUI	TRG608-T6T	D