



ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	C	ECO-13924	1/15/2026	KDANG	DUSTING



### WIRING DIAGRAM



MODEL NUMBER	LENGTH		
	METERS	FEET	TOL. (IN)
U3A00056-03M	0.3	0.98	+/- 1.18
U3A00056-05M	0.5	1.64	+/- 1.18
U3A00056-1M	1.0	3.28	+/- 1.18
U3A00056-2M	2.0	6.56	+/- 1.97
U3A00056-3M	3.0	9.84	+/- 1.97

### NOTES

- ELECTRICAL:  
VOLTAGE TEST: DC 300V 10ms  
INSULATION RESISTANCE: 10.0M Ω, MIN  
CONDUCTANCE RESISTANCE: 5.0 Ω, MAX.
- MOUNTING HARDWARE INCLUDED: 2X #4-40 SCREW
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION LSP-010.

### REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:  
X = ±.2 [5]      FRACTIONS  
XX = ±.02 [0.5]      ± 1/32  
XXX = ±.005 [0.13]      ANGLES ± 1°

CABLE LENGTH TOLERANCES:  
≤12 [305] = +1 [25] / -0  
≥12 [305] ≤ 60 [1524] = +2 [51] / -0  
≥60 [1524] ≤ 120 [3048] = +4 [102] / -0  
≥120 [3048] ≤ 300 [7620] = +6 [152] / -0  
≥300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-COM**  
an INFINITE<sup>®</sup> brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

SCALE      SHEET

NONE

1 OF 1

CA USB-C PNL/USB-CM

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	JYOU	U3A00056	C