

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	INITIAL RELEASE	9/30/13	D.GRIFFIN

## XPFIT FIBER CONNECTOR TERMINATION KIT (FOR XPFIT LC & SC CONNECTORS)



### KIT INCLUDES:

- JACKET AND 250μm FIBER STRIPPER AND 125μm BUFFER REMOVER
- THERMAL BUFFER REMOVAL TOOL
- REPLACEMENT BLADE SET
- PRECISION CLEAVE TOOL (FLAT)
- LINT FREE DRY WIPES
- FIBER OPTIC CLEANING PEN
- KEVLAR SCISSORS
- FIBRE DISPOSAL UNIT
- FINE PERMANENT MARKER PEN
- FIBRE CHECKER
- 2.5mm TO 1.25mm ADAPTER
- SOFT CASE

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE:</p> <p>≤12 [305] = +1 [25] / -0</p> <p>&gt;12 [305] - 60 [1524] = +2 [51] / -0</p> <p>&gt;60 [1524] - 120 [3048] = +4 [102] / -0</p> <p>&gt;120 [3048] - 300 [7620] = +6 [152] / -0</p> <p>&gt;300 [7620] = +5% / -0%</p> <p>ALL OTHER DIMENSIONAL TOLERANCES:</p> <p>.X = .2 [5.08]</p> <p>.XX = .02 [.51]</p> <p>.XXX = .005 [.13]</p>	<p>APPROVALS</p> <p>DRAWN BY D.FRISIELLO</p> <p>CHECKED BY D.GUTTADAURO</p> <p>APPROVED BY D.GALLAGHER</p>		<p>DATE</p> <p>9/26/13</p> <p>9/26/13</p> <p>9/26/13</p>	<p><b>L-com</b> Global Connectivity</p> <p>45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845</p>		
			<p>CATEGORY</p> <p>FIBER OPTICS</p>			
	<p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p>		<p>PRODUCT DESCRIPTION</p> <p>XPFIT-FIBER CNCT TERM KIT</p>			
	<p>PROJECTION</p> 	<p>COLOR VARIATIONS MAY OCCUR</p>		<p>SIZE <b>A</b></p>	<p>FSCM NO. <b>43321</b></p>	<p>DWG. NO. <b>XPFIT-KIT</b></p>
			<p>SCALE: 1:1</p>	<p>CAD FILE: XPFIT-KIT.SLDRW</p>	<p>SHEET 1 OF 1</p>	