

Specifications

PG Size (Male)	PG-11
Cord Dia. Range	0.196" to 0.295" (5.0 to 7.5 mm)
Recommended Mounting Hole	0.750" Dia. (19 mm)
Connector Material	Nylon
Seal Material	Neoprene
Temperature Range	-4° to +176° F (-20° to +80° C)