



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS


REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED FOR PRODUCTION	12/13/01	MCCORMICK
B	REVISED PLATING & LENGTH (ECN 1502)	09/17/03	MCCORMICK
C	ECN 3129: UPDATE DWG FORMAT	12/21/07	D.GRIFFIN



BNC JACK



5/8-24 UNEF INTERNAL THREAD



UHF PLUG

NOTES:

MATERIAL:
BODY: NICKEL PLATED BRASS INSULATOR: DELRIN
CONTACT: GOLD PLATED BRASS

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE
TOLERANCES TO BE: .X ±.1 [2.5] .XX ±.01 [.25] .XXX ±.005 [.13]	DRAWN BY MCCORMICK	12/03/01
OVERALL CABLE LENGTH TOL: ≤ 60 [1524] +3 [76.2] / -0 ≥ 60 [1524] +5% / -0%	CHECKED BY D.PARHAM	12/04/01
PROJ	APPROVED BY R.CARRICK	12/04/01
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE A	FSCM NO. 43321

L-com CONNECTIVITY PRODUCTS	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
CATEGORY	COAXIAL
PRODUCT DESCRIPTION	BNC JACK TO UHF PLUG
SCALE: NONE CAD FILE: BA50.SLDDRW	
SHEET 1 OF 1	