

Premium DVI-I Dual Link DVI Cable Male / Male w/ Ferrites, 10.0ft



CTLDVI-I-MM-10

Configuration

Connector 1	DVI-I Dual Link Male
Connector 2	DVI-I Dual Link Male
Connector 2 Specification	DVI

Mechanical Specifications

Cable Assembly

Temperature

Temperature Operating Range, deg C	0 to +80
Temperature Storage Range, deg C	0 to +40

Size

Length, in [cm]	120 [304.8]
Cable Color	Gray

Cable

Jacket Material	PVC
-----------------	-----

Connector 1

Type	DVI-I Dual Link Male
Configuration	Straight

Connector 2

Type	DVI-I Dual Link Male
Configuration	Straight

Plotted and Other Data

Notes:

- Values at +20 °C, sea level

Premium DVI-I Dual Link DVI Cable Male / Male w/ Ferrites, 10.0ft from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/audio-video-premium-dvi-i-dual-link-dvi-cable-male-male-w-ferrites-100ft>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

CTLDVI-I-MM-10 CAD Drawing
Premium DVI-I Dual Link DVI Cable Male / Male w/ Ferrites, 10.0ft

