

Specifications

Model: SC2404	
Type	4-Way
Frequency	2400 - 2500 MHz
Insertion Loss*	<0.5 dBi
Impedance	50 Ohms
VSWR	<1.5 : 1 Typical
Power Rating	25 Watts
Temperature Range	-40° C to +85° C
Dimensions (L x D x H)	4.6 x 2.6 x 1.7 (inches) 117 x 66 x 43 (mm)
Weight	0.85 lbs. (.39 kg)
Reverse Port Isolation	NO
RoHS Compliant	YES