




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISI

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/12/13	D.GRIFFIN
-	-	-	-
-	-	-	-
-	-	-	-




N-FEMALE  
CONNECTORS  
(3X)



12.4 [315]



12.4 [315]



RoHS Compliant ✓

NOTES:  
PACKAGING:  
COMPONENT SHALL BE PACKAGED IN ACCORDANCE  
WITH L-COM SPEC PKG-00028

-ALL DIMENSIONS FOR REFERENCE-

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
DRAWN BY B.PUCHASKI	02/11/13		<b>L-COM</b> Global Connectivity	
CHECKED BY P.PESA	02/11/13		CATEGORY	
APPROVED BY P.PESA	02/11/13		ANTENNA	
ANGULAR TOLERANCES: ALL = $\pm 1^\circ$	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION 4.9-5.8GHz 17dBi DUAL POLARIZED FLAT PANEL ANTENNA W/N-FEMALE CONNECTORS	
PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>HG4958-17DP-3NF</b>
		REV. <b>A</b>	SCALE: NONE	CAD FILE: HG4958-17DP-3NF.SLDDRW
				SHEET 1 OF 1