

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/14/13	D.GRIFFIN

FRONT VIEW

RIGHT SIDE VIEW

FRONT VIEW
COVER
REMOVED

END VIEW

SECTION A-A

SCREW DOWN
COVER

10-32 X.3125
INSERT X4

MOUNTING PLATE
AND SCREWS SHIPPED
LOOSE WITH EACH
ENCLOSURE

NOTE:

- 1- ENCLOSURE MATERIAL-GRAY (RAL7035)
HOT MOLDED FIBERGLASS REINFORCED POLYESTER
- 2- NEMA RATED TYPE 3, 3R, 3S, 4, 4X, 12 AND 13
PRIOR TO MODIFICATIONS.
- 3- IEC 529 RATED IP 66 PRIOR TO MODIFICATION.
- 4- TEMPERATURE RANGE FROM -50 DEG C TO 150 DEG C.
- 5- SELF EXTINGUISHING AND HALOGEN FREE.
- 6- CABINETS ARE MAINTENANCE FREE AND
CORROSION RESISTANT.
- 7- SHALL BE PACKAGED AS PER L-COM SPEC PKG-00070
- 8- ALL DIMENSIONS FOR REFERENCE ONLY

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005 ANGULAR TOLERANCES: ALL = ± 1° PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY B.PUCHASKI	01/11/13		
	CHECKED BY P.PESA	01/11/13	CATEGORY ENCLOSURE	
	APPROVED BY P.PESA	01/11/13	PRODUCT DESCRIPTION FRP NEMA ENCLOSURE - 12 X 10 X 5 SCREW COVER AND ALUMINUM MNT PLATE	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. NBC121005-KIT
COLOR VARIATIONS MAY OCCUR		SCALE: NONE		CAD FILE: NBC121005-KIT.SLDDRW
		SHEET 1 OF 1		