






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                 |          |           |
|-----------|-----------------|----------|-----------|
| REV       | DESCRIPTION     | DATE     | APPROVED  |
| A         | INITIAL RELEASE | 12/16/11 | D.GRIFFIN |
| -         | -               | -        | -         |
| -         | -               | -        | -         |



- NOTE:  
1- ENCLOSURE MATERIAL-GRAY (RAL7035)  
HOT MOLDED FIBERGLASS REINFORCED POLYESTER  
2- NEMA RATED TYPE 3, 3R, 3S, 4, 4X, 12 AND 13 PRIOR TO MODIFICATIONS.  
3- IEC 529 RATED IP 66 PRIOR TO MODIFICATION.  
4- TEMPERATURE RANGE FROM -50 DEG C TO 150 DEG C.  
5- SELF EXTINGUISHING AND HALOGEN FREE.  
6- CABINETS ARE MAINTENANCE FREE AND CORROSION RESISTANT.  
7- SHALL BE PACKAGED AS PER L-COM SPEC PKG-00070  
8- ALL DIMENSIONS FOR REFERENCE -



RoHS Compliant ✓

|                                                                                                                                                                                                          |                             |                                  |                                                                                             |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|----------------------------------|---------------------------------------------------------------------------------------------|
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONS ARE IN INCHES [mm]<br><br>DIMENSIONAL TOLERANCES:<br><br>.X = ±.1<br>.XX = ±.01<br>.XXX = ±.005<br><br>ANGULAR TOLERANCES:<br>ALL = ± 1°<br><br>PROJECTION<br> | APPROVALS                   | DATE                             | <br>45 BEECHWOOD DRIVE<br>NORTH ANDOVER, MA<br>01845                                        |
|                                                                                                                                                                                                          | DRAWN BY<br>B.PUCHASKI      | 12/14/11                         |                                                                                             |
|                                                                                                                                                                                                          | CHECKED BY<br>M.MARTINEZ    | 12/14/11                         |                                                                                             |
|                                                                                                                                                                                                          | APPROVED BY<br>M.MARTINEZ   | 12/14/11                         |                                                                                             |
| CONFIGURATION DETAILS OF<br>UNDIMENSIONED FEATURES<br>MAY VARY<br><br>COLOR VARIATIONS<br>MAY OCCUR                                                                                                      | CATEGORY<br><br>ENCLOSURE   |                                  | PRODUCT DESCRIPTION<br>NEMA ENCLOSURE 18x16x8 WEATHERPROOF<br>WINDOWED W/DIN MOUNTING RAILS |
|                                                                                                                                                                                                          | SIZE<br><b>A</b>            | FSCM NO.<br><b>43321</b>         |                                                                                             |
|                                                                                                                                                                                                          | DWG. NO.<br>NBW181608-000DR | REV.<br><b>A</b>                 |                                                                                             |
|                                                                                                                                                                                                          | SCALE: NONE                 | CAD FILE: NBW181608-000DR.SLDDRW |                                                                                             |