


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/3/11	D.GRIFFIN



NOTE

1. MATERIAL: .06" [1.52] THK COLD ROLLED STEEL
2. FINISH: FLAT BLACK POWDER COAT
3. COUPLER SHIPPED WITH DUST CAPS INSTALLED. (NOT SHOWN)
4. PACKAGE IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. PARHAM	08/02/2011		
	CHECKED BY D. CASTRO	08/02/2011	CATEGORY RACK PANELS	
	APPROVED BY M. MARTINEZ	08/02/2011	PRODUCT DESCRIPTION 3.5"X19" PNL/12 SC DPX CPL BLK	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. UPR35-12DSCB
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: UPR35-12DSCB.SLDDRW	REV. A
		SHEET 1 OF 1		