


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/8/11	D.GRIFFIN



NOTES:


MATERIAL: .06 THICK COLD ROLLED STEEL.

FINISH: FLAT BLACK POWDER COAT.

KIT INCLUDES (4) 6-32 UNC-2A PAN HEAD SCREWS.

COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D.FRISIELLO	8/4/11		
	CHECKED BY M.SEDLESKI	8/4/11	CATEGORY	
	APPROVED BY M.MARTINEZ	8/4/11	SUB PANELS	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION	
	COLOR VARIATIONS MAY OCCUR		SUB PANEL C6 RJ45/110 4 PORT BLK	
SIZE A		FSCM NO. 43321	DWG. NO. USP4MK-C6B	REV. A
SCALE: NONE		CAD FILE: USP4MK-C6B.SLDDRW		SHEET 1 OF 1