

Specifications

Electrical	
Insertion Loss	Up to 5/32 Inch (4 mm) Thick
Mechanical	
Mating	NMO/TAD Threaded Coupling
Mating Torque	15 inch pounds (170 N.cm) Max.
Cable Attachment	Braid Crimp
Center Conductor Cable Attachment	Solder
Cable Retention	45 lbs. Pull
Material	
Body	Brass
Contact	Gold Plated Brass
Insulator	TFE
Environmental	
Temperature Range	-55C(-67F) to +85C(+185F)
Temperature Cycling	MIL-Std. 202
Weatherproof	Yes
Moisture Resistance	MIL-Std. 202
Corrosion	MIL-Std. 202
Vibration	MIL-Std. 202
Altitude	MIL-Std. 202