





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	APPROVRD FOR PRODUCTION BY STEVE SMITH	01/09/03	MCCORMICK
B	ECN5091: ADDED PACKAGING NOTE, ROHS STAMP, UPDATED FORMAT.	10/19/10	DFF
.	.	.	.
.	.	.	.



NOTES:

1. MATERIAL: COLD ROLLED STEEL 0.024" THK
2. FINISH: BRIGHT CHROME PLATE
3. CONNECTOR HARDWARE SUPPLIED:
TWO #4 JACKSCREWS
TWO #4 SLOTTED SCREWS
TWO #4 HEX NUTS
TWO RETAINING CLIPS
4. FOR USE WITH TWO DB25 OR HD44 D-SUBMINIATURE CONNECTORS
5. ADAPTOR COVERS INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY MCCORMICK	DATE 07/12/02	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CHECKED BY D.PARHAM APPROVED BY R.CARRICK	DATE 12/04/02 12/04/02	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION DB25 SHIELDED ADAPTOR COVERS	
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
		DWG. NO. DHS25	REV. B
		SCALE: NONE	CAD FILE: DHS25.SLDDRW
			SHEET 1 OF 1

D
C
B
A

D
C
B
A

8 7 6 5 4 3 2 1

8 7 6 5 4 3 2 1