






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	DRAWING REPLACES MD44FJR-001	10/21/14	D.FRISIELLO



WIRE CHART	
DIN CONNECTOR	WIRE CODE
PIN1	BLACK
PIN 2	WHITE
PIN3	RED
PIN4	GREEN



- NOTES:
1. FINISH OF EXTERNAL METAL PARTS NICKEL PLATED.
 2. THE D-FLAT ON THE THREADED BARREL OF ADAPTER MUST BE ALIGNED AS SHOWN ABOVE.
 3. WIRE LEADS ARE 26AWG STRANDED TINNED COPPER WITH PVC INSULATION.
 4. EIGHT INCH WIRES CUT BLUNT.
 5. SILK SCREEN PART NUMBER AND COMPANY NAME USING BLACK INK ON FACE SHOWN.
 6. REAR OF HOUSING TO BE POTTED. MATERIAL; SILICONE RESIN CONFORMAL COATING. COLOR; BLACK
 7. 1/2-28 HEX NUT AND INTERNAL TOOTH WASHER INCLUDED.
 8. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.


REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES (mm)
OVERALL CABLE LENGTH TOLERANCE:
≤12 [305] ≤60 [1524] = +.2(5) / -0
>60 [1524] ≤120 [3048] = +.4 [102] / -0
>120 [3048] ≤300 [7620] = +.6 [152] / -0
>300 [7620] = +.8 [203] / -0
ALL OTHER DIMENSIONAL TOLERANCES:
X = ±.2 [5.08]
XX = ±.02 [5.1]
XXX = ±.005 [1.3]

APPROVALS	DATE
DRAWN BY RON CARRICK	12/28/99
CHECKED BY AFC	12/28/99
APPROVED BY AFC	12/28/99

L-com Global Connectivity 45 BEECHWOOD DRIVE
NORTH ANDOVER, MA 01845

CATEGORY	AUDIO/VIDEO		
PRODUCT DESCRIPTION	ADPT, MD44F/LEADS BLKHD R MNT		
SIZE	FSCM NO.	DWG. NO.	REV.
B	43321	MD44FJR	A



SCALE: 1:1 CAD FILE: MD44FJR.SLDDRW SHEET 1 OF 1