


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	07/12/17	J.YOU



PIN OUT	
P1	P2
1	3 RED
2	1 RED
3	2 RED
6	15 RED
7	16 RED
9	6 YELLOW
10	4 YELLOW
11	5 YELLOW
14	18 YELLOW
15	17 YELLOW
16	19 YELLOW
17	9 BLACK
18	7 BLACK
19	8 BLACK
22	11 BLACK
23	10 BLACK
24	12 BLACK
SHELL	SHELL

NOTES:

Electrical Properties:

1. It should be no any open/short, miswiring and intermitten failures.
2. The cable shall be 100% electrical test.
3. Voltage test: DC 300V 10MS;
Insulation resistance: 5.0M ohm/min;
Conductance resistance: 5.0 ohm/max.

Machinery Character:

1. All dimension are "mm/inch" except specified.
2. The cable should be clean, free of oiled/flash/burred.
3. Package: individually packaged in a clear polybag.
4. Cable Ass'y shall be RoHS Compliant.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [.13] PROJECTION 	APPROVAL\$4	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845	
	DRAWN BY J.YOU	07/12/17		
	CHECKED BY B.GATES	07/12/17		
	APPROVED BY B.GATES	07/12/17		
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY AUDIO/VIDEO		PRODUCT DESCRIPTION DVI24+5M-HDMI-AM	
COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. VIC00013	REV. A
SCALE: NONE		CAD FILE: VIC00013.SLDDRW		SHEET 1 OF 1