




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES EC535D-OD1	9/25/14	D.FRISIELLO




WIRING MAP	
RJ45K JACK	RJ45 PLUG
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8

#### NOTES:

1. JACKS ACCEPT RJ45 KEYED PLUGS.
2. MATERIAL:  
CONTACTS: GOLD PLATED  
HOUSING: ABS; COLOR: IVORY
3. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
4. COMPONENT SHALL BE TESTED FOR CONTINUITY.
5. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%  ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13]	APPROVALS	DATE	<div><div>L-com</div><div>Global Connectivity</div></div> <div>45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845</div>			
	DRAWN BY DOUG PARHAM	3/19/2001				
	CHECKED BY T. CLARK	3/20/2001	CATEGORY			
	APPROVED BY C. McCORMICK	3/27/2001	TELECOM/MODULAR			
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION  SOCKET SAVER (8X8)M TO (8X8)KF			
PROJECTION 	COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>EC535D</b>	REV. <b>A</b>
			SCALE: NONE	CAD FILE: EC535D.SLDDRW	SHEET 1 OF 1	