


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


| REVISIONS |                                           |          |             |
|-----------|-------------------------------------------|----------|-------------|
| REV       | DESCRIPTION                               | DATE     | APPROVED    |
| A         | INITIAL RELEASE                           | 02/09/05 | M.LAHEY     |
| B         | ECN# 2462 KIT IS UNASSEMBLED WHEN SHIPPED | 07/07/06 | MCCORMICK   |
| C         | ECN 5405: RE-MODELED AND RE-DIMENSIONED   | 3/25/11  | D.FRISIELLO |



#### NOTES:

1. MATERIAL: .06 THICK COLD ROLLED STEEL.
2. PANEL FINISH: FLAT BLACK POWDER COAT.
3. SILKSCREEN COLOR: WHITE.
4. PANEL SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.
5. EACH KIT CONSISTS OF ONE RACK PANEL AS SHOWN ABOVE, AND 32 INSULATION DISPLACEMENT TYPE RJ45 KEYSTONE JACKS. JACKS HAVE PRESS-ON COVERS THAT PROPERLY PUNCH DOWN THE 24AWG OR 26AWG CONDUCTORS.
6. JACKS ARE U.L. LISTED COMMUNICATIONS CIRCUIT DEVICES.

**RoHS Compliant** ✓

|                                                                                                                                                                                                                                                                                                                                                                |                                                          |                              |                                                                                                                                     |                          |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------|------------------------------|-------------------------------------------------------------------------------------------------------------------------------------|--------------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]<br>OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +3% / -0%<br>ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ±.2<br>.XX = ±.02<br>.XXX = ±.005 | APPROVALS                                                | DATE                         |  45 BEECHWOOD DRIVE<br>NORTH ANDOVER, MA 01845 |                          |
|                                                                                                                                                                                                                                                                                                                                                                | DRAWN BY<br>M.LAHEY                                      | 02/09/05                     |                                                                                                                                     |                          |
|                                                                                                                                                                                                                                                                                                                                                                | CHECKED BY<br>D.PARHAM                                   | 02/09/05                     | CATEGORY<br>RACK PANELS                                                                                                             |                          |
|                                                                                                                                                                                                                                                                                                                                                                | APPROVED BY<br>C.MCCORMICK                               | 02/09/05                     | PRODUCT DESCRIPTION<br>2U x 19" PANEL, 32 KEYSTONE CUTOUTS                                                                          |                          |
| PROJECTION<br>                                                                                                                                                                                                                                                            | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY |                              | SIZE<br><b>A</b>                                                                                                                    | FSCM NO.<br><b>43321</b> |
| COLOR VARIATIONS MAY OCCUR                                                                                                                                                                                                                                                                                                                                     |                                                          | DWG. NO.<br><b>PR35-3206</b> | REV.<br><b>C</b>                                                                                                                    | SCALE: NONE              |
|                                                                                                                                                                                                                                                                                                                                                                |                                                          | CAD FILE: PR35-3206.SLDDRW   | SHEET 1 OF 1                                                                                                                        |                          |