




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED TO PRODUCTION	8/27/01	R. CARRICK
B	ECN# 1528: REMOVED SCREWS, MALE SIDE, ADDED VIEW TO SHOW LABEL	10/1/03	T. CLARK
C	ECN# 1628: ADDED COMPONENT SPECIFICATION TABLE	12/31/03	T. CLARK
D	ECN 4547: REVISED SCREW LENGTH AND NEW FORMAT	2/9/10	D. FRISIELLO



24 CONTACT
FEMALE GPIB CONNECTOR



24 CONTACT
MALE GPIB CONNECTOR



NOTES:

MATERIAL:
HOUSING: DIE-CAST ALUMINUM ALLOY.
CONNECTOR INSULATORS: GLASS-FILLED PBT, BLUE, UL94V-0 RATED.
CONNECTOR CONTACTS: 24X, COPPER ALLOY, RIBBON, .085" PITCH.
THUMBSCREWS: STEEL.

FINISH:
HOUSING: NICKEL PLATED.
CONNECTOR CONTACTS: 30μ INCHES GOLD PLATED OVER NICKEL.
THUMBSCREWS: BLACK OXIDE.

ELECTRICAL:
VOLTAGE RATING: 200 VOLTS.
CURRENT RATING: 1 AMP PER CONTACT AT 25°C.
INSULATION RESISTANCE: 1 GIGAOHMS

MISCELLANEOUS:
OPERATING TEMPERATURE RANGE: -40°C TO +85°C.
WIRED STRAIGHT THROUGH, PIN TO LIKE-NUMBERED PIN AND MEETS ANSI/IEEE STD 488.1-1987.
TWO DUST CAPS PROVIDED FOR CONNECTORS (NOT SHOWN).
ALL DIMENSIONS ARE FOR REFERENCE ONLY.
COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY RON CARRICK	8/27/2001				
	DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.02 .XXX = ±.005	CHECKED BY DOUG PARHAM	8/27/2001	CATEGORY IEEE-488		
		APPROVED BY C. MCCORMICK	8/27/2001	PRODUCT DESCRIPTION IEEE-488 EXTENSION ADAPTOR, M/F		
ANGULAR TOLERANCES: ALL = ± 1°	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. CIB24X	REV. D
PROJECTION 	COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: CIB24X.SLDDRW	SHEET 1 OF 1	