


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	APPROVED FOR PRODUCTION PER STEVE SMITH	10/08/02	MCCORMICK
B	ECN 3798: CN RELEASE AND NEW FORMAT	1/29/09	D.FRISIELLO
.	.	.	.
.	.	.	.



MODEL NUMBER	LENGTH	
	METERS	FEET
CSM94X-1M	1.0	3.28
CSM94X-2M	2.0	6.56
CSM94X-3M	3.0	9.84

WIRING TABLE		
"P1" TYPE 1 CONNECTOR	"J1" TYPE 1 CONNECTOR	WIRE DESCRIPTION
PIN 1	PIN 1	22AWG
PIN 2	PIN 2	22AWG
PIN 3	PIN 3	SHIELDED TWISTED PAIR
PIN 4	PIN 4	
PIN 5	PIN 5	SHIELDED TWISTED PAIR
PIN 6	PIN 6	
SHELL	SHELL	OVERALL SHIELD
PIN 2	PIN 2	PAIR ONE SHIELDING
		PAIR TWO SHIELDING

- NOTES:
- CABLE ASSEMBLY CONSTRUCTED TO MEET THE REQUIREMENTS OF THE IEEE-1394 (FIREWIRE) SPECIFICATION.
 - CONTACT FINISH 30µin GOLD (MINIMUM), OVER 50µin NICKEL (MINIMUM).
 - TWISTED PAIRS INDIVIDUALLY SHIELDED. SHIELDS TIED TOGETHER AND TIED TO PIN 2.
 - CABLE OVERALL SHIELD CONNECTED TO METAL SHELLS OF BOTH PLUGS. OVERALL SHIELD ISOLATED FROM TWISTED PAIRS' SHIELDS.
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN A POLY BAG.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS DRAWN BY MCCORMICK CHECKED BY D.PARHAM APPROVED BY R.CARRICK	DATE 09/25/02 09/25/02 09/25/02	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY FIREWIRE
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION CBL, IEEE1394 TYPE 1 EXT
	SCALE: NONE	SIZE A	FSCM NO. 43321 DWG. NO. CSM94X-1M