


Specifications



Construction Specification		
	Material	Diameter (mm / in)
1. Inner Conductor	Solid Copper	0.94 / 0.037
2. Dielectric	Physical Foam Polyethylene	2.79 / 0.110
3. Outer Conductor	Bonded Aluminum Foil + Tinned Copper Braid	3.53 / 0.139
4. Jacket	White Polyvinyl Chloride - FRPVC	4.95 / 0.195

Electrical Characteristics	
Capacitance (pF/m)	83.3
Impedance (ohm)	50
Velocity (%)	80
Inner Conductor DC Resistance (Ω /km)	24.9
Outer Conductor DC Resistance (Ω /km)	16.1
Shielding Effectiveness (dB)	> 90
Cutoff Frequency	41 GHz
Peak Power	2.5KW

Mechanical and Environmental Characteristics	
Min. Bend Radius (mm / in)	25 / 1.0
Operating Temp. (°C)	-20 to + 60
Tensile Strength (kg / lb)	18.2 / 40
Cable Weight (kg/m - lb/ft)	0.035kg/m 0.022lb/ft
RoHS Compliant	Yes

Attenuation and Avg. Power (20°C)		
Frequency (MHz)	Attenuation dB (100m / 100ft)	Avg. Power (KW)
30	6.5 / 2.0	0.89
50	8.4 / 2.6	0.68
150	14.6 / 4.4	0.39
220	17.70 / 5.4	0.32
450	25.5 / 7.8	0.22
900	36.5 / 11.1	0.15
1500	47.7 / 14.5	0.12
1800	52.5 / 16.0	0.11
2000	55.4 / 16.9	0.10
2500	62.4 / 19.0	0.09
5800	98.1 / 29.9	0.06